THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
G	14

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	G1	REVISED PER ECO-11-004917	11MAR11	RK	HMR

1 FOR .050 TO .082 WIRE INSULATION DIA

2 TONGUE MATERIAL THK = .018±.002

3 APPLIES FROM THE METAL EDGE OF THE BARREL TO THE CENTER OF THE STUD



QTY	DESCRIPTION	MATERIAL & FINISH	PART NO
100	LOOSE PIECE, BOX	BODY: PHOS BRONZE PER ASTM-B103 TIN PLATE PER ASTM-B545 SLEEVE: COPPER PER ASTM-B152 TIN PLATE PER ASTM-B545 INSULATION: NYLON PER ASTM-D4066 TYPE 1, COLOR: YELLOW	8-52924-1
4,000	52924 ON TAPE		52924-1
1	WIRE TERMINAL		52924

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± .008
3 PLC	± -
4 PLC	± -
ANGLES	± 5°

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DWN jr ruth 09MAR10
CHK TOM MICHIELUTTI 09MAR10
APVD TOM MICHIELUTTI 09MAR10
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

TE Connectivity

NAME: WIRE TERMINAL, PIDG, SPRING SPADE WIRE SIZE: 26-22

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-52924	—

CUSTOMER DRAWING | SCALE 8:1 | SHEET 1 OF 1 | REV G1

1470-19 (3/11)

Downloaded from Arrow.com.