**Part Number :** 351504209
**Product Description :** VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Blue, Glow-Wire Capable
**Series Number :** 35150
**Status :** Active
**Product Category :** Connector Housings



## Documents and Resources

### Drawings

351504209_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

351500000AS_ENG-000.pdf

351500000AS_KOR-000.pdf

PK-35150-002-001.pdf

PS-35150-003-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Connector Housings |
| Series | 35150 |
| Description | VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Blue, Glow-Wire Capable |
| Application | Wire-to-Wire |
| Component Type | Receptacle |
| Product Name | VersaBlade |
| UPC | 822350369442 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Physical

| | |
|---|---|
| Circuits (maximum) | 2 |
| Color - Resin | Blue |
| Gender | Receptacle |
| Glow-Wire Capable | Yes |
| Keying to Mating Part | No |
| Lock to Mating Part | Yes |

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Resin | PET/PC |
| Net Weight | 1.706/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 6.20mm |
| Pitch - Termination Interface | 6.20mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +110°C |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| VersaBlade Hybrid Plug Housings | 35151 |

### Use with Part(s)

| Description | Part Number |
|---|---|
| VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Natural | 351500290 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red | 351500292 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Yellow | 351500293 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Blue | 351500294 |
| VersaBlade Male Crimp Terminals | 35745 |



Downloaded from Arrow.com.