



SBPH100375WE2.5 Product Details

 [Share](#)

 [Print](#)

 [Email](#)



SBPH100375WE2.5

TE Internal Number: CN9941-000

 [Active](#)

Label ID Products

[Not reviewed for RoHS Compliance](#)

Product Highlights:

- Printer Type = Thermal Transfer
- Label Height = 95.30 mm
- Label Width = 25.40 mm
- Translucent Vinyl Material
- SBP Series

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Material](#) = Translucent Vinyl
- Series = SBP
- [Color](#) = Clear (White Printable Area)

Electrical Characteristics:

- [Printer Type](#) = Thermal Transfer
- [Number of Labels Across](#) = 1
- Web Width (mm [in]) = 100.30 [3.950]

Body Features:

- Recommended Printer = TE 3000 Series, T200
- Recommended Ribbon = TMS-RJS-RIBBON-4RPSCE

Industry Standards:

- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

Printer/Label Features:

- [Label Height \(mm \[in\]\)](#) = 95.30 [3.750]
- [Label Width \(mm \[in\]\)](#) = 25.40 [1.000]
- [Label Finish](#) = Gloss/Matte
- Tamper Evident = No
- [Label Type](#) = Die-Cut
- Adhesive Type = Permanent Acrylic
- Vertical Repeat (mm [in]) = 28.60 [1.125]
- Printable Height (mm [in]) = 25.40 [1.000]

Environmental:

- [Operating Temperature \(°C \[°F\]\)](#) = -51 - +93 [-60 - +200]

Conditions for Usage:

- Energy Product = No

Packaging Features:

- [Packaging Quantity](#) = 2,500

Other:

- Brand = Raychem

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

