

Plug Component			Plug Strip Dimension			Wire Spec.	Terminal ROJ & Strip			Terminal Component		
Color	Component	Qty	Strip	ROJ	Color	H05VV-F 0.75mm²X3C BLACK	Strip	ROJ	Color	Component	Color	Qty
40P Black 90±5°A	CEE 7/7 (LT-312(16A 250V))	1	9±1	25±3	Blue	Length: 2000±50 mm	7±1	20±3	Blue	IEC 320 C13 (LT-501(10A 250V))	40P Black 90±5°A	1
BLACK	(312 Inner Body)	1	9±1	25±3	Brown		7±1	20±3	Brown	computer power cord terminals	Copper	3
			9±1	25±3	Yellow-green		7±1	20±3	Yellow-green	(501 Inner Body)	White	1

MARKING:

RHYTHM: <PS>E JET R63003 ROHS 60227 IEC 53 RVV CCC A075833 CE CB KEMA-KEUR ◁VDE▷ IEMMEQU CEBEC 957 RT-502 OVE H05VV-F 3G0.75mm² 300/500V N/11600 OC3-75 3x0.75mm² V-75 4V-75 250/440V RHYTHM R

NOTE：

1. PLUG：LT-312 EUROPEAN TYPE
2. CONNECTOR：LT-501 IEC-320 C13
3. CORD：H05VV-F 0.75mm²X3C BLACK 2M
4. APPROVALS：FIMKO SEMKO NEMKO DEMKO KEMA CEBEC DEMKO VDE OVE EAC
5. Supplier for flexible cord：RHYTHM
6. Hi-Pot Test:2000v/1min<1mA>

Modification History

	DESCRIPTION	DATE

DRAWER	Eric	DATE	20/10/19	P/N	800-0.75-14X-BL-00200-1
APPROVE		REV.	0	Dr.No.	1090634
		比 例		TOL.	±5mm
				ALL DIMENSIONS IN mm	

CnC Tech

Industrial Cable and Connector Technology

Downloaded from Arrow.com.