Hello, We use cookies to create the most secure and effective website possible. By using this site, you consent to the use of cookies. See full details in our Privacy Statement.

Click here to not show this message again

1LS9

Overview

MICRO SWITCH LS Series General Purpose Limit Switches, Side Rotary - Lever Not Included, 1NC 1NO SPDT Snap Action, Double Break, 0.5 in - 14NPT conduit, Compact/Non-Plug-

View More

view all 1LS9 literature
view distributor inventory
sample request
email support
get support
email sales
find a distributor
email this page

Technical Specifications

Availability	Global
Full Overtravel Force	8,13 N m [6 in lb] max.
Pretravel (PT)	5° max.
Product Type	MICRO SWITCH Compact Limit Switches
Termination Type	0.5 in - 14NPT Conduit

Operating Force (OF)	0,51 N m [4.5 in lb] max.
Release Force	0,08 N m [0.75 in lb] min.
Overtravel (OT)	30° min.
Actuator	Side Rotary
Circuitry	1NC 1NO SPDT Snap Action, Double Break

View More

View documents in: English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
MICRO SWITCH LS Series General Purpose Limit Switches	Datasheet	English	5MB
PK 81028: LS Limit Switches	Installation Instructions	English	397KB
PK 81241: Gold contact LS	Installation Instructions	English	16KB
MICRO SWITCH Limit Switches Comparison	Product Range Guide	English	460KB

View More

Product Features

- Mode of operation is field adjustable
- NEMA 1, 3, 4, 6, and 13
- Wide choice of heads and actuators
- Variety of operating characteristics
- Captive screws
- UL and CSA approved parts available

Applications

Downloaded from Arrow.com.

- Machine tools
- Conveyors
- Material handling
- Metal fabrication equipment
- Lift trucks

COPYRIGHT © 2018 HONEYWELL INTERNATIONAL INC.

Downloaded from Arrow.com.