Rubber Feet *1421-FEET Series*



- Made from Polyurethane material, except 1421T7 which is made from SBR Rubber.
- Service temp rating is -34°C to 66°C (-30°F to 150°F).
- For best adhesion results:
  - Clean surfaces with isopropyl alcohol (rubbing alcohol).
  - Apply firm pressure to generate good initial contact.
  - Adhesion bond will increase over time.

RoHS

Gallery



	Qty Per Package	Style	Width / Diameter	Height	Color	Attachment Method	Adhesive Type
1421T2	24	Flat Round	0.50	0.14	Black	Self-Adhesive	Natural Rubber R-30
1421T2CL	24	Flat Round	0.50	0.14	Clear	Self-Adhesive	Acrylic A-20
1421T2GY	24	Flat Round	0.50	0.14	Gray	Self-Adhesive	Natural Rubber R-30
1421T3	24	Square	0.50	0.23	Black	Self-Adhesive	Natural Rubber R-30
1421T4	24	Square	0.81	0.30	Black	Self-Adhesive	Natural Rubber R-30
1421T5BK	24	Round Hemisphere	0.44	0.20	Black	Self-Adhesive	Natural Rubber R-30
1421T5CL	24	Round Hemisphere	0.44	0.20	Clear	Self-Adhesive	Acrylic A-20
1421T6CL	24	Flat Round	0.31	0.09	Clear	Self-Adhesive	Acrylic A-20
1421T7	24	Round	0.75	0.55	Black	Screw-On	N/A
1421T8BK	24	Square	0.47	0.12	Black	Self-Adhesive	Natural Rubber R-30
1421T9BK	24	Round	0.88	0.40	Black	Self-Adhesive	Natural Rubber R-30

1421T7 attaches with a #8 x 1/2" screw.

Tags: **feet**, **foot**, **rubber foot**, **tabletop**, **desktop**, **anti-skid**, **no skid**

Data subject to change without notice.

Downloaded from Arrow.com.

© 2026. Hammond Manufacturing Ltd. All rights reserved.

Downloaded from Arrow.com.