

Home → Tool Types → Screwdrivers → Precision Hex Metric Screwdrivers

# Precision Hex Metric Screwdrivers



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

| SKU   | Product                                 | Size Hex Metric | OAL MM | Blade Length Inch | Price | Qty                            |
|-------|-----------------------------------------|-----------------|--------|-------------------|-------|--------------------------------|
| 26307 | Precision Hex Driver .7 (.028") x 40mm  | 0.7mm           | 120    | 1.6               |       | <input type="text" value="0"/> |
| 26309 | Precision Hex Driver .9 (.035") x 40mm  | 0.9mm           | 120    | 1.6               |       | <input type="text" value="0"/> |
| 26313 | Precision Hex Driver 1.35 (.050") x40mm | 1.3mm           | 120    | 1.6               |       | <input type="text" value="0"/> |
| 26315 | Precision Hex Driver 1.5 x 50mm         | 1.5mm           | 145    | 2                 |       | <input type="text" value="0"/> |
| 26320 | Precision Hex Driver 2.0 (5/64") x 50mm | 2.0mm           | 145    | 2                 |       | <input type="text" value="0"/> |
| 26325 | Precision Hex Driver 2.5 x 60mm         | 2.5mm           | 170    | 2.4               |       | <input type="text" value="0"/> |
| 26330 | Precision Hex Driver 3.0 x 60mm         | 3.0mm           | 170    | 2.4               |       | <input type="text" value="0"/> |
| 26340 | Precision Hex Driver 4.0 x 60mm         | 4.0mm           | 170    | 2.4               |       | <input type="text" value="0"/> |

Add to Cart



Add to Wishlist



Share on Facebook



Tweet This



Pin it

We accept

amazon pay

## Frequently bought together



Price for all selected :

Add selected to cart

This item: [Precision Hex Metric Screwdrivers](#)

☒ [Pocket Clip For Precision Screwdrivers](#)

☒ [Green Canvas Pouch for Sets](#)

☒ [Precision Hex Inch PicoFinish Screwdrivers](#)

☒ [PicoFinish Precision Hex Metric Screwdrivers](#)

☒ [Precision Hex Inch Screwdrivers](#)

## Details

Wiha special chrome-vanadium-molybdenum tool steel  
Through hardened for best wear resistance  
Corrosion protective Vapor Chrome Finish  
Exact fit precision CNC machined tips  
Precision handle is made of high quality cadmium free plastic  
Molded on handle for permanent bond to blade  
The tapered faceted shape allows rapid rotation  
Handles are proportioned to blade size for optimum torque  
Finger tip rotation cap for precise turning and control  
Professional Quality Made In Germany

## Additional Info

Head Type

●● hex metric

Country of  
Manufacture

Germany

Handle Grip  
Types

Precision

## WRITE YOUR OWN REVIEW


Only registered users can write reviews. Please, [log in](#) or [register](#)

## Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

~ View Full Warranty

## You may also be interested in the following product(s)



Precision Hex Metric Screwdrivers

## Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

## Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



## Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge Gmbh](#)  
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm  
CST USA**

1348 Dundas Cir,  
Monticello, MN 55362  
Customer Service Email:  
[cservice@wihatools.com](mailto:cservice@wihatools.com)  
Tel: 763-295-6591  
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools  
In Stock**



**Newsletter**

[Subscribe](#)