

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 TYCO ELECTRONICS CORPORATION ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	26JUN2017	RZ	IY
	A1	INCREASE PN	14SEP2022	X.F	E.J
	A2	ADD PN	12DEC2023	W.Z	E.J
	A3	ECN-24-263260	19APR2024	W.Z	E.J




D-D




2310469-1/-2/-4




1-2310469-3/-4/-5/-6





1-2310469-3/-4/-5/-6




2310469-1/-2/-4










E-E



1. MATERIAL :
   TYPE : PA66 GF30 V0 FLAME RETARDANT MATERIAL
   COLOR : SEE TABLE

2. FEATURES DENOTED BY REFERENCE DIMENSIONS MUST BE INSPECTED FOR PRESENCE

3. PART MUST BE FREE OF EXCESSIVE FLASH, MIS-MATCH, SINK MARKS, OR OTHER VISUAL IMPERFECTIONS THAT MAY AFFECT PRODUCT FIT FORM OR FUNCTION

4. CIRCUIT ID

5. FOR HB VERSION REFER TO DRAWING 2103181

-1 AS SHOWN

COLOR	WIRE O.D. MIN	WIRE O.D. MAX	F	DESCRIPTION	TE P/N
RED	4.50	5.10	5.10	CABLE SEAL RETAINER, SIZE D	2310469-4
BLACK	4.00	4.40	4.50	CABLE SEAL RETAINER, SIZE E	1-2310469-6
BLACK	5.48	6.10	6.20	CABLE SEAL RETAINER, SIZE C	1-2310469-5
BLACK	4.76	5.48	5.60	CABLE SEAL RETAINER, SIZE B	1-2310469-4
BLACK	4.20	4.70	4.80	CABLE SEAL RETAINER, SIZE A	1-2310469-3
DK GRAY	5.48	6.10	6.20	CABLE SEAL RETAINER, SIZE C	2310469-2
ORANGE	4.76	5.48	5.60	CABLE SEAL RETAINER, SIZE B	2310469-1

A3

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±1
1 PLC ±0.2
2 PLC ±0.10
3 PLC ±0.100
4 PLC ±0.0001
ANGLES ±1°

MATERIAL 1 -
FINISH - -

DWN R.ZHANG 13OCT2016
CHK SY WANG 26JUN2017
APVD I YIN 26JUN2017
PRODUCT SPEC 108-2394
APPLICATION SPEC 114-13295
WEIGHT -

TE Connectivity

NAME CABLE SEAL RETAINER HVA280-2PHI XE -

SIZE A1 | CAGE CODE 00779 | DRAWING NO C-2310469 | RESTRICTED TO -

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV A3

Downloaded from Arrow.com.