

3M United States >

Scotch-Brite™ Clean and Finish Roll, CF-RL, A/O Medium, 6 in x 30 ft, 2 per case

Part Number 476T33, 3M ID 61201302017, UPC 00048011002743

★ ★ ★ ★ ★

(0)

Write a review



[View Images](#)

- Cut-to-fit roll stock provides uniform finishing, blending, polishing, contour finishing, and cleaning
- Conformable pad gets into hard-to-reach areas
- Suitable for hand use or on oscillating and dual pad rubbing machines
- Open web material resists loading, allowing abrasives to maintain a consistent cut-rate

[View all details](#)

Specifications

Application	Finishing , Sanding , Surface Preparation
Application Category	Adhesives , Blending/Deburring , Coatings , Finishing/Polishing , Sanding Wood by Hand , Sealant Corrosion Removal
Brand	Scotch-Brite™
Color	Red , Maroon
Equipment - Machines	Dual Pad Rubbing Machines , Hand Sanding , Oscillating Machines
For Use On	All Metals , Hardwood
Front Color	Maroon
Grade	Medium
Industries	Marine , Metalworking , MRO , Woodworking
Length	30 Foot
Length (Metric)	9.14 m

Low Stretch	No
Mineral Type	Aluminum Oxide
Position	Better
Primary Application	Other Door Assembly Applications
Product Form	P1400/R3500
Sub Industries	Cabinetry , Custom Woodworking and Millwork , Furniture , Metal Fabrication , Primary Wood and Panel Processing
Substrate	All Metals , Hardwood , Softwood
TDS Required	Yes
US Govt Contract Number	GS-21F-0075x
Width	6 in
Width (Metric)	152.4 mm

Product Details

- Cut-to-fit roll stock provides uniform finishing, blending, polishing, contour finishing, and cleaning
- Conformable pad gets into hard-to-reach areas
- Suitable for hand use or on oscillating and dual pad rubbing machines
- Open web material resists loading, allowing abrasives to maintain a consistent cut-rate
- Suitable for metal, wood, composite and advanced materials

Scotch-Brite™ Clean and Finish Roll delivers consistent results for finishing, blending, polishing, and cleaning on a variety of metals, wood, plastics surfaces as well as hard-to-reach areas. The roll stock can be easily cut to any length. Clean and Finish roll stock provides consistent surface conditioning for the life of the product.

Load resistance keeps the abrasive particles exposed to maintain a consistent cut rate. Our general purpose pad can be cut and used by hand for precise control. Wider width stock can be cut and paired with a hand pad holder for uniform finishing, or on an inline or oscillating sander to cover larger areas.

We manufacture Scotch-Brite™ Clean and Finish Rolls with a choice of silicon carbide, aluminum oxide, or talc abrasive mineral. Silicon carbide is a synthetic mineral that is very sharp and commonly used for low-pressure applications such as paint prep and finishing. Aluminum oxide is a hard, blocky mineral that provides high cut-rate and long life. While silicon carbide breaks down faster than aluminum oxide, it produces a finer finish. Talc is a mild abrasive that can be used achieve a satin finish or with polish to create a high gloss finish in topcoat rubbing applications.

Our Scotch-Brite™ abrasives are unique surface conditioning products with abrasives incorporated into non-woven fiber matrix. Combining abrasives and non-woven material creates an abrasive system that delivers consistent results for the life of the product. The open-web material runs cool and is load resistant, which keeps the abrasive minerals cutting at high performance by limiting clogging of the fibers.

[Learn more about 3M Abrasive Systems Scotch-Brite™ Hand Finishing Systems](#) (PDF, 1 Mb)

Resources

Customer Reviews

Reviews



Be the first to review this product

Large Volume Order

If you are considering a large purchase of this or other 3M Abrasive products our inside sales team is ready to help by providing additional information and options that our industrial customers typically seek when making abrasive procurement decisions. Our technical expertise, customer support, and global capabilities put us in a unique position to address your biggest challenges, and we'll do our best to prove that we should be your abrasive supplier of choice.

All fields are required unless indicated optional

* First Name

* Last Name

* Company

* Company Address

* Contact Phone

* Email Address

* Country/Region

Select One

* City

* Zip Code

* Number of Abrasive Discs or Wheels You Plan to Purchase

* Total Number of Operators in your shop

Select One

☒ **Subscribe to our mailing list**

3M takes your privacy seriously. 3M and its authorized third parties will use the information you provided in accordance with our [Privacy Policy](#) to send you communications which may include promotions, product information and service offers.

Please be aware that this information (including the original and the subsequent reply) may be transferred to a server located in the U.S. for metrics and storage. If you do not consent to this use of your personal information, please do not use this system.

SEND

3M United States

PRODUCTS

[Abrasives](#)
[Adhesives & Tapes](#)
[Advanced Materials](#)
[Films](#)
[Filtration](#)
[View All Products](#)

INDUSTRIES

[Automotive](#)
[Commercial Solutions](#)
[Consumer](#)
[Design & Construction](#)
[Electronics](#)
[Energy](#)
[Government](#)
[Health Care](#)
[Manufacturing](#)
[Mining, Oil & Gas](#)
[Safety](#)
[Transportation](#)

BRANDS

[Post-it](#)
[Scotch](#)
[Scotch-Brite](#)
[Command](#)
[Filtrete](#)
[Nexcare](#)
[ScotchBlue](#)

HELP

[Help Center](#)
[Site Map](#)

REGULATORY

[SDS, RDS, More Regulatory & Compliance Information](#)
[Transport Information Search](#)
[Transparency in Supply Chains and Modern Slavery Disclosures](#)

NEWS

[News Center](#)
[Particles by 3M](#)
[Press Releases](#)

ABOUT US

[About 3M](#)
[3M Careers](#)
[Investor Relations](#)
[Partners & Suppliers](#)
[Sustainability](#)
[3Mgives](#)
[Ethics & Compliance](#)

SEARCH 3M



FOLLOW US



[Change Location](#)

United States - English



[Legal](#) | [Privacy](#) | [DMCA](#)
© 3M 2019. All Rights Reserved.

The brands listed above are trademarks of 3M.