



Tandem®

Call to order: 1-866-IRISOUS

[Show Mates](#)

Packaging Number

IMSA-10109S-60Y902

Category: [Board to Board Connectors](#)

Series: 10109

Drawings

Product 2D: [PDF](#) Packaging 2D: [PDF](#) Product Spec: [PDF](#)

Product Details

Floating: Yes

Floating Type: Box

Connection Orientation: Straight/Vertical

Pitch: 0.635

Pin Count: 60

Plating: Gold

Mount: SMT

Boss Type: Location pin

Vacuum Tape Included: Yes

Terminal Material: Corson

Part Height: 8.5

Base

Base Number: C

Mold Material: LCP/9T

Packaging Type: Tape

Environmental

Beryllium & Halogen Free: Yes

Advanced

Rating Voltage AC / DC: 50 volts/ 50 volts

Current Rating: 0.5A

High Speed: No

Data Transfer Rate (Gbps): 3

Inquire About This Product

*Full Name***Email Address**

IMSA-10109S-60Y902

*Message**[Get Started](#)

Related Technologies




Floating

Reduce assembly error and relieve stress on solder joints with Iriso Floating technology.

[Learn More](#)

Two Point Contact

Increases the chances of proper contact by cleaning and adding a redundant two-point-contact.

[Learn More](#)

Z-Move

Keep critical applications running smoothly with Iriso Z-Move.

[Learn More](#)[IRISO Home](#) > [Products](#) > [Product](#)

Products

[Find A Product](#)[Board to Board Connectors](#)
[FFC/FPC Connectors](#)
[Compression Connectors](#)
[Pin Header Connectors](#)
[Socket Connectors](#)
[Interface Connectors](#)
[ESD / Card Connectors](#)
[Input / Output Connectors](#)[Find a Mate](#)

Product Info

[Board to Board Connectors](#)
[FFC/FPC Connectors](#)
[Compression Connectors](#)
[Pin Header Connectors](#)
[Socket Connectors](#)
[Interface Connectors](#)
[ESD / Card Connectors](#)
[Input / Output Connectors](#)

Technologies

[Floating](#)
[Two Point Contact](#)
[Z-Move](#)
[I-Lock](#)
[Auto I-Lock](#)

Industries

[Aerospace](#)
[Automotive](#)
[Consumer Electronics](#)
[Industrial Automation](#)
[Medical](#)
[Network / Telecom](#)
[Appliances](#)

Other

[About IRISO](#)
[News & Stories](#)
[Help & FAQs](#)
[Sitemap](#)
[Contact Us](#)

Intl. Sites

[Japan](#)
[Korea](#)
[China](#)