

2-Port Desktop KVM Switch with 2 KVM Cable Kits (PS2)

MODEL NUMBER: **B022-002-KT-R**



Description

Tripp Lite's B022-002-KT-R 2-port KVM Switch is the optimal solution for controlling 2 computers from one keyboard, mouse and monitor. Installation is a snap - just connect the PCs using the included PS/2 cable kits. P776-Series USB KVM cable kits are available separately for connection of USB computers. Easily switch between computers via front-panel push buttons or keyboard hotkey commands.

Features

- Control 2 computers from a single keyboard, mouse, and monitor
- Comes with 2 PS/2 KVM cable kits
- P776-Series USB KVM cable kits are available separately for connection of USB computers
- Supports VGA, SVGA, or Multisync monitors
- Easy to install - no software required
- Easily select a computer via front-panel push buttons or keyboard hotkeys
- Auto Scan function to monitor computer operation
- Supports Microsoft IntelliMouse and the scrolling wheel on most mice
- Superior video quality - up to 2048x1536; DDC2B
- External power not required
- Compatible with all major operating systems except Mac and Sun

Specifications

OVERVIEW	
UPC Code	037332120236
Console	No
Max CPU	2

Highlights

- Control 2 computers with 1 keyboard, monitor and mouse
- Comes with 2 PS/2 KVM cable kits
- P776-Series USB KVM cable kits are available separately for connection of USB computers
- Simple plug-and-play design
- Ultra-slim design takes up minimal space
- Compatible with all major operating systems except Mac and Sun

System Requirements

- VGA, SVGA or Multisync Monitor with an HD15 port
- PS/2 mouse
- PS/2 keyboard
- PS/2 or USB computer
- Compatible with all major operating systems except Mac and Sun

Package Includes

- B022-002-KT-R 2-port KVM Switch
- (x2) PS/2 KVM Cable Kits
- PS/2 console cable kit
- Owner's Manual

Technology	PS/2; VGA/SVGA
PHYSICAL	
Color	Silver
Cable Jacket Color	Silver
LCD Monitor (cm)	Not Applicable
LCD Monitor (in.)	Not Applicable
Shipping Dimensions (hwd / in.)	6.80 x 2.50 x 9.40
Shipping Dimensions (hwd / cm)	17.27 x 6.35 x 23.88
Shipping Weight (lbs.)	2.00
Shipping Weight (kg)	0.91
Unit Dimensions (hwd / in.)	1.250 x 5.000 x 3.500
Unit Dimensions (hwd / cm)	2.54 x 12.7 x 8.26
Unit Weight (lbs.)	0.73
Unit Weight (kg)	0.33
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys
IP Remote Access	No
CONNECTIONS	
Number of Ports	2
PC/Server Connections	PS/2; USB; VGA
Included KVM Cable (Equipment Side) - Connector 1	HD15 (Male)
Included KVM Cable (Equipment Side) - Connector 2	(x2) MiniDIN6 (Male)
FEATURES & SPECIFICATIONS	
Cat5 KVM Switch	No
NIAP-Certified Secure	No
Number of Users	1
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.