Part Number : 2028281506
Product Description : Mirror Mezz Hermaphroditic Connector, 2.50mm Connector Height, BGA-Attach Mounting, 6 Pair, 15 Row, 404 Circuits, 0.76µm Gold (Au) Plating, with Pegs
Series Number : 202828
Status : Active
Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

2028281506_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

2028281506EE-000.pdf

2028281506SP-000.zip

Specifications

2028280001-AS-000.pdf

2028289005PS-001.pdf

2028280001-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	202828
Description	Mirror Mezz Hermaphroditic Connector, 2.50mm Connector Height, BGA-Attach Mounting, 6 Pair, 15 Row, 404 Circuits, 0.76µm Gold (Au) Plating, with Pegs
Application	Board-to-Board, Mezzanine
Component Type	Plug
Product Name	Mirror Mezz
UPC	191128437226

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	0.75A (1 Oz Cu Trace), 1.2A (2 Oz

Downloaded from Arrow.com.

	Cu Trace)
Voltage - Maximum	30V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	404
Circuits (maximum)	404
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	No
Lock to Mating Part	No
Mated Height	5.00mm
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.330/g
Number of Rows	15
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	1.50mm, 4.00mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	BGA Solder

Downloaded from Arrow.com.

Solder Process Data

Max-Duration	20
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mirror Mezz Hermaphroditic Connectors	202828
Mates With	This is a hermaphroditic, self-mating part.

Downloaded from Arrow.com.