




**Part Number :** [561618181](#)

**Product Description :** 2.00mm Pitch DuraClik Crimp Terminal, Female, 26-22 AWG, Gold (Au) Plating, Bag

**Series Number :** 56161

**Status :** Active

**Product Category :** Crimp Terminals



---

## Documents and Resources

### Drawings

[561618181\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[AS-54992-005-001.pdf](#)

[AS-54992-006-001.pdf](#)

[561619200-200.pdf](#)

[PS-502351-002-001.pdf \(Gold Plating\)](#)


### Tooling Specifications

[CS-56161-003-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

## Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	56161
Description	2.00mm Pitch DuraClik Crimp Terminal, Female, 26-22 AWG, Gold (Au) Plating, Bag
Application	Automotive, Signal, Wire-to-Board
Product Name	DuraClik
UPC	800756476674

### Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	125V

### Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	18.300/mg

Packaging Type	Bag
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.40mm max.
Wire Size (AWG)	22, 24, 26
Wire Size mm <sup>2</sup>	N/A

## Mates With / Use With

### Use with Part(s)

Description	Part Number
DuraClik Single Row Receptacle Housings	<u>502351</u>

---

## Application Tooling

### Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Micro-Latch, DuraClik, and Servo Motor Encoder Female Terminals, 26-22 AWG	<u>638235100</u>

---

This document was generated on May 19, 2026