
S05MTA235 Product Details



S05MTA235

TE Internal Number: 3-1618259-6

Obsolete

Contact Product Information Center

High Voltage Relays

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O
- Power Switching = No
- Contact Current Rating = 0 - 5 A
- Not RF Rated
- Coil Voltage = 12 VDC

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- None Available

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Termination Style = PCB Tail

Electrical Characteristics:
- Contact Current Rating (A) = 0 - 5
- RF Rated = No
- Coil Voltage (VDC) = 12
- Voltage, Max. (VDC) = 0 - 15000
- Current, Carry Only = Yes

Termination Related Features:
- High Voltage Connection (Power) = PCB Tail
- High Voltage Connection (Coil) = PCB Tail
- Auxiliary Contacts = Without

Body Related Features:
- Mount Style = Printed Circuit Board

Configuration Related Features:
- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O
- Power Switching = No
- Economizer = Without

Industry Standards:
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:
- Brand = Kilovac

© 2010 Tyco Electronics All Rights Reserved | Privacy Policy

Provide Website Feedback

Downloaded from Arrow.com.