

COIL:

RESISTANCE 90 Ω ±10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 6.7 VDC

MUST RELEASE 1.0 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 13 MS MAX.
RELEASE TIME 5 MS MAX.
CONTACT BOUNCE 5 MS MAX. (NC)
2 MS MAX. (NO)

CUST. HI-G
CUST. NO. 2T-1B-112

TYPE 07 RELAY

CUSTOMER DATA SHEET

BLUE BEAD



CONTACT RATING: 10A 30 VDC RES
10A 115 VAC 400 Hz, 6A 30 VDC
INDUCTIVE 100,000 OPERATIONS

DR. R.B. 4-16-91 CK. 4/16/91

Communications Instruments, Inc.

B07B932BZ1-8004

Downloaded from Arrow.com.