© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

WIRE AND CABLE

HOOK UP WIRE



✔ Active

TE CONNECTIVITY (TE)

99M0111-22-3

Raychem | SP

99M0111-22-3
TE Internal Number: 9580173001
Alias ID: 1-1197416-3

EU RoHS Compliant
EU ELV Compliant

Cable Type Spec 99M

Voltage Rating (V) 600

Insulation Material Radiation-Crosslinked, Modified Polyester

Conductor Material Tin-Plated Copper

Wire Size (AWG) 22

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

Customer Drawing
PDF
English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Downloaded from Arrow.com.

Cable Type Spec 99M
Cable Style Primary
Product Classification Cable - Spec 99 & 100
Product Type Cable

Configuration Features

Number of Strands 19
Number of Conductors 1

Electrical Characteristics

Voltage Rating (V) 600

Body Features

Insulation Material Radiation-Crosslinked, Modified Polyester
Conductor Material Tin-Plated Copper
Wire Color Orange

Dimensions

Strand Size (AWG) 34
Wire Size (AWG) 22
Wire Size (mm^2) .326
Conductor Diameter .79 mm [.031 in]
Insulation Thickness .15 mm [.006 in]
Overall Outside Diameter 1.2 mm [.0473 in]
Wire Diameter 1.05 mm [.041 in]

Usage Conditions

Operating Temperature Range (°C) -55 – 125

Other

Wire Source United Kingdom

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.