


Rev	AWO #	Description	Date	Appr
-		RELEASED	11/18/20	

APPROVED: _____


DATE: _____ TITLE: _____







RECOMMENDED
PANEL CUT–OUT



CIRCUIT DIAGRAM
(SPST)

SPECIFICATIONS:
Material:
Body: PA66, Color: Black
Lever: Brass, Nickel plated
Terminal: Brass, Silver plated
Electrical:
Rating: 1.5A @ 250V AC
3A @ 125V AC
Contact resistance: 20 mΩ max
Insulation resistance: 1000 MΩ min (500VDC)
Dielectric withstanding voltage: 1000V AC for 1 minute
Electrical Life: 10,000 cycles
Temperature Rating:
Operating temperature: −25°C to +85°C
Environmental:
Lead free, RoHS compliant

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	OW	11/18/20
CHECKED	AC	11/18/20
APPROVED		

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: SWITCH, TOGGLE SUB-MINIATURE, SPST, ON-OFF, SOLDER TYPE

SIZE	PART NO.	REV.
X	SW-T3-1A-A-A3-S1	-

REF: - SCALE: NTS SHEET 1 OF 1

Downloaded from Arrow.com.