

3SBM1065A2 Product Details

 Share  Print  Email



 Active

 View 3D PDF

Military/Aerospace High Performance Relays

3SBM1065A2=M39016/31-003L

3SBM1065A2 (2-1617516-9)

TE Internal Number: 2-1617516-9

Product Highlights [View All](#)

- 3SBM 1/5-Size Relay Series
- Input Voltage = 26.5 VDC
- Contact - Arrangement = 4 Form C, 4PDT, 4 C/O
- Contact - Rated Current = 2 A
- Polarized, Bistable Coil - Magnetic System

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features	
MOSFET Driver	Without
Mechanical Attachment	
Mounting Options	PC Board
Electrical Characteristics	
Input Voltage (VDC)	26.5
Contact - Rated Current (A)	2
Coil Suppression Diode	Without
Coil Polarity Protection Diode	Without
Coil - Resistance (Ω)	975
Coil Power Measurement	Milliwatts
Coil - Rated Power, DC (mW)	720
Actuating System	DC
Shock	100G's, 6ms
Vibration	30G's, 10 to 3000Hz
Termination Features	
Termination Type	PC Pins

Body Features	
Enclosure Type	Hermetically Sealed
Configuration Features	
Contact - Arrangement 	4 Form C, 4PDT, 4 C/O
Coil - Magnetic System	Polarized, Bistable
Transistor Driver	Without
Coil Latching	Double
Industry Standards	
Government/Industry Qualification	Yes
Government/Industry Part Number	M39016/31-003L
RoHS/ELV Compliance 	Not ELV/RoHS compliant
Lead Free Solder Processes 	Not suitable for lead free processing
Approved Standards	M39016 Qualified, L Level
Conditions for Usage	
Temperature Range (°C)	-65 – +125
Other	
Series	3SBM 1/5-Size Relay
Brand	CII

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

About TE

Investors

News Room

Supplier Portal

Careers

Terms & Conditions

Privacy Policy

Global Accessibility Statement

Quick Links

Distributor Inventory

Product Cross Reference

Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support

Email or Chat With Us

Find a Phone Number

Knowledge Base

Manage Your Account

Keep Me Informed

