Data Sheet | Item Number: 211-504

Shrink tube; for Smart Printer; Unshrunk diameter: 9.5 mm; 15 m on roll; white

https://www.wago.com/211-504



Color: white

Similar to illustration

Technical data

Suitable	for wire cross-section 10 … 16 mm²
Marking method	Thermal transfer
Delivery form	Roll
Delivery form configuration	15 m/roll
Printing device	Smart Printer (thermal transfer printer)

Physical data

Depth	0.185 mm

Mechanical data

Mounting type	Sliding on conductor
Shrink rate	2:1
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data

Color	white
Material	Polyolefin
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	without adhesive
Halogen-free	Yes
Weight	328.3 g

Downloaded from Arrow.com.

Environmental requirements

Ambient temperature (storage)	+10 … +25 °C
Ambient temperature (operation)	-55 … +125 °C
Relative humidity	45 … 55 %

Commercial data

PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DK
GTIN	4055143370295
Customs tariff number	39173200900

Product Classification

UNSPSC	39121703
eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-04-01
ETIM 9.0	EC001530
ETIM 10.0	EC001530
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 211-504

Documentation

Operating Instructions

211-502 Information on printing material	1 28.08.2020	pdf 1059.74 KB	

Downloaded from Arrow.com.