



Color: orange

Similar to illustration

Transformatorenklemmen Serie 711 mit CAGE CLAMP®

Bei diesen Transformatorenklemmen mit der Artikelnummer 711-175 steht ein schneller und zuverlässiger Anschluss im Fokus. Diese Transformatorenklemmen benötigen für den Leiteranschluss eine Abisolierlänge zwischen 9 und 10 mm . Dieses Produkt verwendet die CAGE CLAMP®-Technologie. Mit dem CAGE CLAMP® Universalanschluss steht Ihnen eine zuverlässige und wartungsfreie Anschlusstechnik zur Verfügung, um sämtliche Leiterarten mithilfe einer Käfigzugfeder anzuschließen. Es ist keine Vorbehandlung der Leiter notwendig, beispielsweise durch das Aufcrimpen von Aderendhülsen. Die Abmessungen sind in Breite x Höhe x Tiefe (37,5 x 35 x 23,5) mm.

Electrical data

Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	-	800 V	-
Rated surge voltage	-	8 kV	-
Rated current	-	25 A	-

Connection data

Clamping units	5	Connection 1	
Total number of potentials	5	Connection technology	CAGE CLAMP®
Number of connection types	1	Strip length	9 ... 10 mm / 0.35 ... 0.39 inches
		Pole number	5

Physical data

Width	37.5 mm / 1.476 inches
Height	35 mm / 1.378 inches
Depth	23.5 mm / 0.925 inches



Material data		
Note (material data)		Information on material specifications can be found here
Color		orange
Material group		I
Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0
Fire load		0.361 MJ
Weight		17.3 g

Commercial data		
PU (SPU)		50 pcs
Packaging type		Box
Country of origin		DE
GTIN		4044918853828
Customs tariff number		85369010000

Product classification		
UNSPSC		39121410
eCl@ss 10.0		27-14-11-10
eCl@ss 9.0		27-14-11-10
ETIM 9.0		EC000398
ETIM 8.0		EC000398
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 60998	NTR NL-7194
CCA DEKRA Certification B.V.	EN 60998	2160584.54
CSA DEKRA Certification B.V.	C22.2 No. 158	1101145
UL UL International Germany GmbH	UL 1059	E45172

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
UK-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-



Downloads			
Environmental Product Compliance			
Compliance Search			
Environmental Product Compliance 711-175			↓

Documentation			
Additional Information			
Technical Section	03.04.2019	pdf 2027.26 KB	↓

CAD/CAE-Data			
CAD data		CAE data	
2D/3D Models 711-175		EPLAN Data Portal 711-175	↓
		ZUKEN Portal 711-175	↓