Part Number : 15975081
Product Description : Mini-Fit TPA Receptacle Housing, 4.20mm Pitch, Dual Row with Secondary Terminal Retention, 8 Circuits, Black
Series Number : 30067
Status : Active
Product Category : Connector Housings
Engineering Part Number : 30067-08A2



Documents and Resources

Drawings

015975081_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PK-30067-001-001.pdf

PS-45750-001-001.pdf

PS-5556-003-001.pdf

TS-30067-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	30067
Description	Mini-Fit TPA Receptacle Housing, 4.20mm Pitch, Dual Row with Secondary Terminal Retention, 8 Circuits, Black
Application	Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. See Molex product specification PS-45750-001 for additional current derating information. Connector Position Assurance
Component Type	Receptacle
Product Name	Mini-Fit TPA
UPC	800754202169

Agency

CSA	LR19980
UL	E29179

Downloaded from Arrow.com.

Physical

Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	2.640/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit TPA Dual Row Plug Housings	30068
Mini-Fit TPA Dual Row Vertical Headers	30069
Mini-Fit TPA Dual Row Right-Angle Headers	30070

Use with Part(s)

Description	Part Number
Mini-Fit TPA Keys	30072
Mini-Fit Connector Position Assurance Key	30071

Downloaded from Arrow.com.

Mini-Fit Female Crimp Terminals	5556
Mini-Fit Plus Female Crimp Terminals	45750

Downloaded from Arrow.com.