

① Order code:A-MCSSP60XXX : color Grey

order lengths in meter:
0.5,1,2,3,5,7,10,15,20,30

① Order code:A-MCSSP60XXX/X

order lengths in meter:
0.5,1,2,3,5,7,10,15,20,30

order color: (R)Red,(Y)Yellow,
(G)Green,(B)Blue

Electrical test:
Open/Short/intermittence: 100%

PIN OUT

CN1	WIRE COLOR	CN2
1	WHITE	1
2	ORANGE	2
3	WHITE	3
6	GREEN	6
4	BLUE	4
5	WHITE	5
7	WHITE	7
8	BROWN	8
SHELL	BRAID	SHELL

② Tolerance

Length(meter)	Max-M	Min-M
0.5	+0.03	-0.025
1	+0.04	-0.035
2	+0.06	-0.06
3	+0.09	-0.09
5	+0.15	-0.15
7	+0.21	-0.21
10	+0.3	-0.3
15	+0.45	-0.45
20	+0.6	-0.6
30	+0.9	-0.9

③

NO.	NAME.	Q'TY	SPECIFICATION
3	Molding PVC	2	Molding PVC 45P
2	RJ45 CONN	2	RJ45 8P8C,Two Fork gold plated contacts 3u" with metal housing
1	CABLE	1	CAT6 S/FTP(26AWG*1PR-A)*4+B+PVC OD:5.8±0.2mm

RoHS compliant
Unit: mm

Scale	FREE
TOLERANCE	
DIM	TOL
Angle	TOL

Id.	Modification	Date	Name
③	Update the cable description	01.11.2018	Segal
②	Clarify the tolerance	23.08.2018	Segal
①	Add Grey color order code	11.08.2016	Ray
⓪	Drawn	01.02.2016	Joanna

	Date	Name
Drawn	01.02.2016	Joanna
Approved	01.11.2018	Amy

ASSMANN WSW components

Customer-No.

ASSMANN WSW-No.
A-MCSSP60XXX/X

Drawing-No.
ASS 7542 CA

rev03

Replace

Sheet

Downloaded from Arrow.com.