Data sheet

# IE-TO-USB

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Mounting rail outlet, USB coupling (A-A) design according to IEC 61076-3-107

## General ordering data

| | |
|---|---|
| Version | Terminal rail outlet, USB, IP20 |
| Order No. | 8946960000 |
| Type | IE-TO-USB |
| GTIN (EAN) | 4032248734955 |
| Qty. | 1 items |



Downloaded from Arrow.com.

# Data sheet

## IE-TO-USB

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | |
|---|---|
| Net weight | 31.3 g |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | | Operating temperature | -40 °C...70 °C |
| Installation temperature | | | |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### General Info

| | | | |
|---|---|---|---|
| Connection 1 | USB A | Connection 2 | USB A |
| Wiring | USB | Colour | Light Grey |
| Housing main material | PA UL 94 V0 | Type of mounting | TS 35 |
| Protection degree | IP20 | | |

### General standards

| | |
|---|---|
| Connector standard | IEC 61076-3-107 |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000313 | ETIM 9.0 | EC000313 |
| ETIM 10.0 | EC000313 | ECLASS 14.0 | 27-44-03-20 |
| ECLASS 15.0 | 27-44-03-20 | | |




Downloaded from Arrow.com.

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

### Dimensioned drawing







Downloaded from Arrow.com.

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Accessories

## Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.
Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.
Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

| | | |
|---|---|---|
| Type | ESG 9/11 K MC NE WS | Version |
| Order No. | 1857440000 | ESG, Device markers x 11 mm, PA 66, Colour: white, Self-adhesive |
| GTIN (EAN) | 4032248402731 | |
| Qty. | 200 ST | |



Downloaded from Arrow.com.