



ADIPX-X-LC-R

Z - Tin Plated
G - Gold Plated

Number of Contacts
08/10/14/16/20/24/28/40











POSITION	A	B
24P	35.73	27.94
28P	40.81	33.02
32P	45.89	38.10
36P	51.00	43.18
40P	56.20	48.26

Material:
- Insulator Material: PBT+30%GF(UL94V-0)
- Contact Material: Brass or Phosphor Bronze
- Underplate: Nickel
- Contact Area: 1μ"~30μ" Selective Gold

Electrical:
- Current Rating : 1AMP
- Insulation Resistance: 1000Ω Min
- Dielectric Withstanding: 500 V AC
- Operation Temperature: -55°C to +105°C

RoHS Complaint

Scale	1:1							Name
TOLERANCE						Drawn	10.28.11	Chappell
X.X	±0.40					Approved		
X.XX	±0.25							
X.XXX	±0.15							
Angle	±3°							
			Modification	Date	Name			

ASSMANN WSW components

Item No.
ADIP-x-x-LC-R

Title DIP Plug, 2.54MM Pitch, PCB Mount

Drawing No.

rev00

Replace

Sheet

Downloaded from Arrow.com.