
2157375-1 Product Details



2157375-1

TE Internal Number: 2157375-1

Active

Circular HD Connectors

Not EU RoHS or ELV Compliant

Product Highlights:

- Connector
- Shell Size = 2
- Black Chromate Shell Finish
- Connector Style = Receptacle
- Contact Type = Socket

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Documentation & Additional Information

Product Drawings:

- CIRCULAR HD RECEPTACLE WITH SOCKET CONTACTS JAM NUT,... (PDF, English)
- CIRCULAR HD PLUG WITH PIN CONTACTS 8 POS. (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

List all Documents

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Shell Size = 2
- Shell Finish = Black Chromate
- Connector Design = Circular
- Panel Thickness (mm [in]) = 3.00 [0.118]
- Key Type = Single Key
- Termination Style = Panel

Mechanical Attachment:

- Panel Attachment Style = Rear Mount

Electrical Characteristics:

- Current Rating (A) = 2.5

Body Features:

- Number of Positions = 8

Contact Features:

- Contact Type = Socket
- Contact Size = 0.7 mm

Housing Features:

- Connector Style = Receptacle

Industry Standards:

- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Hand solderable with tin/lead solder

Other:

- Brand = AMP

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved

Downloaded from Arrow.com.