


[Products](#)[Industries](#)[Resources](#)[About TE](#)[My Account](#)[Innovation](#)[Support Center](#)

[Home](#) > [Products](#) > [Relays](#) > [Product Feature Selector](#) > [Product Details](#)

HMS1201S108P Product Details

[Share](#)[Print](#)[Email](#)

 **Active**

 [View 3D PDF](#)

Military/Aerospace High Performance Relays

HMS1201S108P = M39016/44-008P

HMS1201S108P (2-1617039-4)

TE Internal Number: 2-1617039-4

Product Highlights [View All](#)

- HMS Half-Size Relay Series
- Input Voltage = 5 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact - Rated Current = 2 A
- Non Polarized, Monostable Coil - Magnetic System

[Pricing & Availability](#)[Request Sample](#)[Add to My Part List](#)[Buy Product through Distributor](#)[Feedback](#)[Documents](#)[Features](#)[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

MOSFET Driver Without

Mechanical Attachment

Mounting Options PC Board

Electrical Characteristics

Input Voltage (VDC) 5

Contact - Rated Current (A) 2

Coil Suppression Diode Without

Coil Polarity Protection Diode Without

Coil - Resistance (Ω) 47

Coil Power Measurement Milliwatts

Coil - Rated Power, DC (mW) 532

Actuating System DC

Shock 50G's, 11ms

Vibration 20G's, 10 to 2500Hz

Termination Features

Termination Type PC Pins

Body Features

Enclosure Type Hermetically Sealed

Configuration Features

Contact - Arrangement 2 Form C, DPDT, 2 C/O

Coil - Magnetic System Non Polarized, Monostable

Transistor Driver Without

Industry Standards

Government/Industry Qualification Yes

Government/Industry Part Number M39016/44-008P

RoHS/ELV Compliance Not ELV/RoHS compliant

Lead Free Solder Processes Not suitable for lead free processing

Approved Standards M39016 Qualified, P Level

Conditions for Usage

Temperature Range (°C) -65 – +125

Other

Series HMS Half-Size Relay

Brand CII

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

