
202K232-25-11-0 Product Details



Active

Molded Parts

202K232-25-11-0

202K232-25-11-0

TE Internal Number: 952223-000

Product Highlights View All

- VG95343 Parts 6,7,8 and 9
- Molded Part Type = Molded Boot
- Molded Part Shape = Straight
- Molded Part Lip = With Lip
- Operating Temperature = -75 - 150 °C

Pricing & Availability
Request Sample
Add to My Part List
Buy Product through Distributor

[+] Feedback

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Molded Part Type	Molded Boot
Molded Part Shape	Straight
Molded Part Lip	With Lip
Angle	180°
Adhesive Description	Adhesive Purchased Separately
Size	32
Family Name	202K2
Color	Black

Mechanical Attachment

Adhesive Pre-Coating	Without

Dimensions

Expanded ID, Min. (mm [in])	25.00 [0.980]
Recovered ID, Max. (mm [in])	13.80 [0.540]

Body Features

Material	Fluid Resistant Modified Elastomer

Housing Features

Material Systems Code	25
Max. Inside Diameter of Part (mm [in])	13.80 [0.540]

Configuration Features

Material Code	25

Industry Standards

Government/Industry Qualification	No
Approved Standards	VG95343 Parts 6,7,8 and 9
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Environmental

Operating Temperature (°C)	-75 – +150

Operation/Application

Application	General Purpose

Purchasing Information

Adhesive Code	S1017, S1048, S1125

Other

Brand	Raychem

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved | Provide Website Feedback

Downloaded from Arrow.com.