BJ157FFL-2C

DESCRIPTION | SUPPORT | REQUEST QUOTE | DOCUMENTS

TRS Bulkhead Jack, Straight, Flange Mount, 2 Hole Configuration, Solderpot, 4-lug

IN STOCK ✔ | DRAWING

Type	TRS
Termination Style	Receptacle
Termination Type	Solder
Body Style	Straight
Gender	Jack
Mounting Style	Flange Mount
Body Plating	Nickel
Body Material	Brass
Max Frequency	500 MHz
Contact Plating	Gold
Insulated	No
# of Lugs	4

RECOMMENDED PRODUCTS

BJ157F-4C
TRS Twinax/Triax Connectors
See Details

BJ150FL
TRS Twinax/Triax Connectors
See Details

BJ150
TRS Twinax/Triax Connectors
See Details

Copyright © 2017, Bel Fuse Inc. All Rights Reserved.

ecia MEMBER

Downloaded from Arrow.com.