



SPECIFICATION

Performance level	PL2
Filter type	C
Capacitance	3900pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB



PCB Layout, Component side, thickness 1.6 mm



							Dat.	Name			Ma?Mstab/ Scale
						Detail.	8-JUL-02	CV	All Dim. in mm Orig. Size DIN A 4	D-Sub, female, angled, 15 Poles, turned solder pins, board-locks and clinch-nuts	1.5:1
						Insp.	12/01/12	JB			
			36283	12/01/12	SD	Stand.					
09642147243	M3		33262	15/11/05	JMDR	HARTING EURL F-95972 Paris				TB 0964214724x	Blatt/ Page 1/4
09642147242	UNC 4-40		31058	8-JUL-02	CV						
Part number	Nut thread		Mod.	Dat.	Name					Sub.	

Downloaded from Arrow.com.