Part Number : 1063591005
Product Description : Quasar OptiX Field Mountable Connector (FMC), SC/UPC, Singlemode, for 2.00mm Jacketed Cable, Blue Housing
Series Number : 106114
Status : Active
Product Category : Fiber Optic Connectors



Documents and Resources

Drawings

1063591005_sd.pdf

Specifications

1063591003_INS-DTL-000.pdf

1063591001_PS-000.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Fiber Optic Connectors
Series	106114
Description	Quasar OptiX Field Mountable Connector (FMC), SC/UPC, Singlemode, for 2.00mm Jacketed Cable, Blue Housing
Keyword	FMC
Mode	Singlemode
Product Name	Quasar OptiX Field Mountable Connector
UPC	198282470205

Physical

Angled Physical Contact (APC)	No
Boot Color	White
Boot Type	Straight
Cable Size	2.00mm
Color - Resin	Blue
Ferrule Hole Size	N/A
Ferrule Material	Ceramic
Gender	Plug
Material - Housing	PBT
Mounting Style	Pre-Polished
Net Weight	8.000/g
Ports	1
Wire/Cable Type	Simplex

Downloaded from Arrow.com.