Part Number : 330013023
Product Description : MX150 Female Terminal for Unsealed Connectors, Gold Plating, 22 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.
Series Number : 33001
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

330013023_sd.pdf

313025040-000.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-33012-002-001.pdf

AS-33012-002-CH-001.pdf

AS-33012-002-001.pdf

PS-33012-002-001.pdf

TS-33001-002-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34; 33
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	33001
Description	MX150 Female Terminal for Unsealed Connectors, Gold Plating, 22 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.
Application	Wire-to-Board, Wire-to-Wire, Automotive
Comments	Left Reel Payoff, Large Polarization Rib; Not to be used with MX150 Sealed Connectors
Product Name	MX150
UPC	822350084215

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Physical

Gender	Female
Grip Code	22
Material - Metal	High Performance Alloy (HPA)

Downloaded from Arrow.com.

Material - Plating Mating	Gold
Material - Plating Termination	Unplated
Net Weight	0.435/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Terminal Size	1.5
Wire Insulation Diameter	1.70mm max.
Wire Size (AWG)	22
Wire Size mm^2	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
MX150 Mat-Sealed Dual Row Female Connector Assemblies	33472
MX150 Mat-Sealed Single Row Female Connector Assemblies	33471
MX150 Hybrid Mat-Sealed Female Connector Assemblies	34985
MX150 Mid-Voltage Mat-Sealed Female Connector Assemblies	300361
MX150 Mid-Voltage Mat-Sealed Female Connector Assemblies	300363
MX150 Mid-Voltage Hybrid Mat-Sealed Female Connector Assemblies	303367

Application Tooling

Global

Downloaded from Arrow.com.

Description	Part Number
Extraction Toolkit for MX150 Connectors	2002220700
FA2 Mechanical Feed Crimp Applicator for MX150 Terminals, 22 AWG and 0.50mm² Wire	2157860100
FA2 Pneumatic Feed Crimp Applicator for MX150 Termainals, 22 AWG and 0.50mm² Wire	2157860110
PremiumGrade Hand Crimp Tool for MX150 Female Terminals, 22-18 AWG	638116000
Hand Crimp Tool Metric 0.5 and 0.75	638116200
Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to-Motor Terminals	638131500
FineAdjust Applicator for SRC Connector using MX150 Receptacle Terminals, 0.50mm² CHEMINAX 2021D0309 wire	639042000
ServiceGrade Hand Crimp Tool for MX150 Crimp Terminals, 22-14 AWG	640160133

Downloaded from Arrow.com.