Heavy Duty Industrial Outlet Strip *1584 Series*

15A | 125V | 5-15R Outlets



Features

- Built to meet the rugged requirements of commercial and industrial use.
- All metal housing - tough extruded aluminum case with a black powder paint coated steel cover.
- Heavy duty NEMA 5-15R receptacles.
- Mounting feet (with keyhole slots) allow temporary work station mounting if desired.
- On-Off switch is rocker type with pilot light (on units with on-off switch - listed below). A red pilot light is used to indicate power on (on units with no switch).
- **Click here for our surge protected version**.

Specifications

- Heavy duty 14 gauge wire cord - 14/3 SJT type for extreme temperature ranges and integral molded plug.
- Plug types available are NEMA 5-15P straight blade or NEMA L5-15P locking type (see table below).
- Includes 15 amp, 125 volt resettable circuit breaker to prevent accidental line overload.
- UL/cUL Listed Standard UL1363 file No. E166039 & CSA C22.2 No. 308-14 & CSA C22.2 No. 0.4-04
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

Plug Types



5-15P Straight Blade



L5-15P Locking Type

Accessories

- Rack Cabinet Vertical Mount Adaptor

Illuminated On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions Height	Width	Length	Outlet Qty	Outlet NEMA Type	Rotated Outlet	Cord Length (ft)	Plug Type	Plug NEMA Type
1584H4A1	**1584T4A1**	2.33	2.12	10.18	4	5-15R	No	6	Straight	5-15P
1584H4A1RA	**1584T4A1RA**	2.33	2.13	13.36	4	5-15R	Yes	6	Straight	5-15P

Downloaded from Arrow.com.

Illuminated On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions Height	Width	Length	Outlet Qty	Outlet NEMA Type	Rotated Outlet	Cord Length (ft)	Plug Type	Plug NEMA Type
1584H4B1	**1584T4B1**	2.33	2.12	10.18	4	5-15R	No	15	Straight	5-15P
1584H4B1RA	**1584T4B1RA**	2.33	2.13	13.36	4	5-15R	Yes	15	Straight	5-15P
1584H4C1	**1584T4C1**	2.33	2.12	10.18	4	5-15R	No	6	Locking	L5-15P
1584H4C1RA	**1584T4C1RA**	2.33	2.13	13.36	4	5-15R	Yes	6	Locking	L5-15P
1584H4D1	**1584T4D1**	2.33	2.12	10.18	4	5-15R	No	15	Locking	L5-15P
1584H4D1RA	**1584T4D1RA**	2.33	2.13	13.36	4	5-15R	Yes	15	Locking	L5-15P
1584H5A1	**1584T5A1**	2.33	2.12	13.36	5	5-15R	No	6	Straight	5-15P
1584H5B1	**1584T5B1**	2.33	2.12	13.36	5	5-15R	No	15	Straight	5-15P
1584H5C1	**1584T5C1**	2.33	2.12	13.36	5	5-15R	No	6	Locking	L5-15P
1584H5D1	**1584T5D1**	2.33	2.12	13.36	5	5-15R	No	15	Locking	L5-15P
1584H6A1	**1584T6A1**	2.33	2.12	13.36	6	5-15R	No	6	Straight	5-15P
1584H6A1RA	**1584T6A1RA**	2.33	2.13	16.51	6	5-15R	Yes	6	Straight	5-15P
1584H6B1	**1584T6B1**	2.33	2.12	13.36	6	5-15R	No	15	Straight	5-15P
1584H6B1RA	**1584T6B1RA**	2.33	2.13	16.51	6	5-15R	Yes	15	Straight	5-15P
1584H6C1	**1584T6C1**	2.33	2.12	13.36	6	5-15R	No	6	Locking	L5-15P
1584H6C1RA	**1584T6C1RA**	2.33	2.13	16.51	6	5-15R	Yes	6	Locking	L5-15P
1584H6D1	**1584T6D1**	2.33	2.12	13.36	6	5-15R	No	15	Locking	L5-15P
1584H6D1RA	**1584T6D1RA**	2.33	2.13	16.51	6	5-15R	Yes	15	Locking	L5-15P
1584H7A1	**1584T7A1**	2.33	2.12	16.51	7	5-15R	No	6	Straight	5-15P
1584H7B1	**1584T7B1**	2.33	2.12	16.51	7	5-15R	No	15	Straight	5-15P
1584H7C1	**1584T7C1**	2.33	2.12	16.51	7	5-15R	No	6	Locking	L5-15P
1584H7D1	**1584T7D1**	2.33	2.12	16.51	7	5-15R	No	15	Locking	L5-15P
1584H8A1	**1584T8A1**	2.33	2.12	16.51	8	5-15R	No	6	Straight	5-15P
1584H8B1	**1584T8B1**	2.33	2.12	16.51	8	5-15R	No	15	Straight	5-15P
1584H8C1	**1584T8C1**	2.33	2.12	16.51	8	5-15R	No	6	Locking	L5-15P
1584H8D1	**1584T8D1**	2.33	2.12	16.51	8	5-15R	No	15	Locking	L5-15P

Replacement Mounting Foot (One Foot)

Part No.	1584MF

Data subject to change without notice.

© 2026. Hammond Manufacturing Ltd. All rights reserved.

Downloaded from Arrow.com.