



P1		P2
1	NC	1
2	Black	2
3	Red	3
4	Green	4
5	Yellow	5
6	NC	6



5ft ≤ L ≤ 12ft



12ft <L ≤ 50ft

Note for plug:

Material:
Housing-Polycarbonate,clear.
Terminal-0.36[.014] thick phosphor bronze.
Thick gold in localized gold plate.
Area,Gold flash over the remainder.
Over 2.54mm[.000100] thick nickel underplate

Order code: AT-S-26-6/4/X-XX/R

Order color:
B: Black
W: White
S: Silver

Length Code	Length (mm)
5	1525±20(5FT)
7	2135±30(7FT)
10	3050±60(10FT)
12	3660±60(12FT)
14	4270±60(14FT)
25	7625±100(25FT)
50	15250±150(50FT)

RoHS compliant

Unit: mm

Scale	Free						Date	Name
TOLERANCE						Drawn	10.08.2017	Fred
						Approved	10.08.2017	Fred
.x	±0.50							
.xx	±0.20							
DIM	TOL							
		⓪	Drawn	10.08.2017	Fred			
Angle	±2°	Id.	Modification	Date	Name			

Customer-No.

ASSMANN WSW-No.
AT-S-26-6/4/X-XX/R

Drawing-No.
ASS 8044 CA

rev00

Replace

ASSMANN wsw components

KAB0759

Downloaded from Arrow.com.