







Plug Component			Plug Strip Dimension			Wire Spec.	Terminal ROJ & Strip			Terminal Component		
Color	Component	Qty	Strip	ROJ	Color	SJT 18AWGX3C 105°C (GRAY)	Strip	ROJ	Color	Component	Color	Qty
40P clear color 90±5°A	NEMA5-15P HOSPITAL GRADE (LT-205(10A 125V))	1	10±1	21±3	Black		7±1	20±3	Black	IEC 320 C13 (LT-501(10A 125V))	40P clear color 90±5°A	1
Nickel-Plated	ϕ4.75 U Grounding pin	1	10±1	21±3	White	Length: 914±20 mm	7±1	20±3	White	computer power cord terminals	Copper	3
Nickel-Plated	6.3*1.5(Solid Blades)	2	10±1	36±3	Green		7±1	20±3	Green	(501 Inner Body)	White	1
Nickel-Plated	Copper ring	1										

NOTE：

1. PLUG：NEMA5-15P HOSPITAL GRADE (LT-205)
2. CONNECTOR：IEC-320 C13 (LT-501)
3. CORD：SJT 18AWGX3C 105°C GRAY 3FT
4. APPROVALS：UL, C-UL
5. Flexible cord： RHYTHM
6. Hi-Pot Test:2000v/1min<1mA>

MARKING:

RHYTHM: (UL)E88231 SJT 3X18AWG(0.824mm²) 105°c 300V VW-1 CSA LL54496 SJT 3X18AWG(0.824mm²)105°c 300V VW-1 RHYTHM R

Modification History

	DESCRIPTION	DATE

DRAWER	Eric	DATE	20/10/24	P/N	800-18-00D-GR-0003F-1
APPROVE		REV.	0	Dr.No.	1091093
		比 例		TOL.	±5mm
				ALL DIMENSIONS IN mm	

CnC Tech
Industrial Cable and Connector Technology

Downloaded from Arrow.com.