

Part Number : 50291900
Product Description : KK High Pressure Crimp Terminal, Female, 30-24 AWG, Brass, 2.54µm Tin (Sn) Plating, Reel
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : 7879-1(P154)
Packaging Alternative : 469990101 (Bag)

Documents and Resources

Drawings

050291900_sd.pdf

PK-2759-002-001.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-7879-001.pdf

27590000-TS-000.pdf

Part Details

General

Status	Active
Category	Crimp Terminals
Series	7879
Description	KK High Pressure Crimp Terminal, Female, 30-24 AWG, Brass, 2.54µm Tin (Sn) Plating, Reel
Application	Wire-to-Board
Product Name	KK High Pressure
UPC	822348742165

Physical

Gender	Female

Downloaded from Arrow.com.

Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.158/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size (AWG)	24, 26, 28, 30
Wire Size mm^2	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
Extraction Tool for KK 2.54mm Terminals, 30-22 AWG	11030022
Insertion Tool for KK 2.54mm Terminals, 30-22 AWG	638120000
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 28-22 AWG	638190800
Mini-Mac Applicator	638915100

Downloaded from Arrow.com.