HellermannTyton

Technical data sheet

Article number:
111-01626 T40R



Product Group	Cable Ties Polyamide 6.6 standard
Material	Polyamide 6.6 (PA66)
Colour	Natural (NA)

Application Tool	EVOcut, MK7P, MK10-SB, MK20, EVO7i, EVO7iSP
Bundle Ø max.	40.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Halogen-free	Yes
Length (L)	175 mm
Min.Tensile Strength	180 N
Operating Temperature	-40 °C to +85 °C
Package Content	100 pcs.
Package Content packed in	bag
Releasable Closure (Yes/No)	No
Specifications	BV 03856/H0 BV, EN 50149:1999, IEC 62275:2006
Thickness (T)	1.15 mm
Toothing (Serration)	Inside Serrated
UV-Stabilised	No
Variant	Inside Serrated
Weight/Unit	0.000968 kg
Width (W)	4.0 mm

HF RoHS

created on 18. September 2026, 6:48 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.