



Canvas Go! Plus SD memory card

for DSLRs, mirrorless cameras and 4K video

Kingston's Canvas Go! Plus SD is designed for adventurers constantly chasing the perfect shot. With superior transfer speeds of up to 200MB/s¹, the Canvas Go! Plus SD card accelerates your workflow and efficiency so that you'll have more time to take your creativity to new heights on your next journey. Featuring U3 and V30 speed ratings, the Canvas Go! Plus allows you to capture stunning 4K Ultra-HD videos without worrying about slow speeds or dropped frames. It also excels in burst-mode photography, offering smooth, consistent shots. Take your vision on the road with the Canvas Go! Plus SD – where adventure meets creativity.

- Superior transfer speeds of up to 200MB/s¹
- Ideal for shooting 4K UHD video and burst-mode photography on your DSLR
- U3 & V30 speed rating
- Durable

Key Features

- Superior speeds

Transfer Full HD & 4K UHD content faster with speeds of up to 200MB/s¹.

- Larger capacities

Capacities of up to 1TB² to store 4K photos and videos.

- Ideal for shooting 4K UHD video and burst mode photography on your mirrorless

High speeds and improved performance will help accelerate your workflow.

Specifications

Capacities ²	64GB, 128GB, 256GB, 512GB, 1TB
Standard/Class	Class 10, UHS-I, U3, V30
Performance ¹	Up to 200MB/s read (64GB-128GB) Up to 200/160MB/s read/write (256GB-1TB)
Dimensions	24mm x 32mm x 2.1mm
Format	exFAT
Operating temperature	-25°C~85°C
Storage temperature	-40°C~85°C
Voltage	3.3V
Warranty/support	Lifetime

Product Image



Part Numbers

SDG4

SDG4/64GB
SDG4/128GB
SDG4/256GB
SDG4/512GB
SDG4/1TB

1. Based on internal testing; performance will vary based on host device. Engineered with proprietary technology to reach read speeds beyond UHS-I 104MB/s specification, up to 200MB/s. Full performance requires MobileLite Plus Reader.
2. Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the product. For more information go to Kingston's [Flash Memory Guide](#).



THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE.

©2025 Kingston Technology Europe Co LLP and Kingston Digital Europe Co LLP, Kingston Court, Brooklands Close, Sunbury-on-Thames, Middlesex, TW16 7EP, England. Tel: +44 (0) 1932 738888 Fax: +44 (0) 1932 785469 All rights reserved. All trademarks and registered trademarks are the property of their respective owners. MKD-03252025