All orders placed will be shipped out as usual, delivery times are expected to be affected due to COVID-19.Thank you for your continued support. Read More

Register to Get $10 Shipping Coupon



GRIS 150M Miniature WiFi(802.11n) Module

SKU:FIT0628 Brand:DFRobot Reward Points: 85

Quantity Based

QTY	DISCOUNT
3-4	
5-9	
10+	

Quantity: - +

ADD TO CART

Frequently Bought Together

GRIS 150M Miniature WiFi(802.11n) Module + 150M ... Raspberry Pi + Raspberry Pi 3 M... B+ + Raspberry Pi 3 M... A+ + ... Development Board =

You have choosen:0
Total amount:

BUY IT NOW

INTRODUCTION

Does it still bother you that you cannot access the Internet anytime anywhere? Here comes a new mini wireless network card, plug and play. Bring you a fast and stable wireless network!

This is a 150M miniature USB WiFi module that fully complies with IEEE 802.11n standard, up to 150Mbs data rate and more efficient data transmission in LAN. It supports 64/128/256-bit WEP data encryption, as well as WPA/WPA-PSK, WPA2/WPA2-PSK secure authentication mechanism, which greatly improves the security of data transmission.

Besides that, the WiFi module adopts CAA technology to detect signal interference. When there is wireless signal interference around, the bandwidth mode will be adjusted automatically to avoid interference so as to enhance the stability of wireless network. With function of soft router, the wireless card can be used as a router to distribute network to smart-phone and tablet PC. The module can still provide excellent signal receiving ability and steady wireless signal even the intelligent antenna has been integrated into an ultra-compact body.

Besides the commonly used communication device like phone, tablet PC and desktop, the WiFi module can also be suitable with all sorts of mini PC such as Raspberry Pi and PYNQ-Z2 development board.

SPECIFICATION

Downloaded from Arrow.com.

- Wireless Standard: IEEE 802.11B/G/N
- Antenna Gain: 2dBi
- Transmission Speed: 150Mbps (Maximum)
- Transmit Power: 20dBm
- Interface Type: USB2.0
- Support Operating System: Windows 2000 /XP /Vista /WIN7 /WIN8 /WIN10 /LINUX /Mac7 8 9
- Frequency Range: 2.4~2.4835GHz
- Working Environment: non-extreme environment
- Security: WEP, WPA/WPA-PSK, WPA2/WPA2-PSK
- Operating Temperature: 0°C-40°C
- Storage Temperature: -40°C~70°C
- Operating Humidity: 10%~90% RH, non condensing
- Storage Humidity: 5%~90% RH, non condensing
- Package Dimension: 21*14*7mm(L*W*H)/0.83*0.55*0.28”

SHIPPING LIST

- GRIS 150M Miniature WiFi(802.11n) Module x1

REVIEW

FAQ

0 Comments DFRobot Disqus' Privacy Policy Login
Recommend Tweet Share Sort by Best
ırt the discussion...
Be the first to comment.
Subscribe Add Disqus to your site Do Not Sell My Data DISQUS

Sign up for exclusive offers!

Your email address →

Like us on

DFROBOT DRIVE THE FUTURE

INFORMATION

About Us
Warranty
Privacy Policy
Shipping
Payment
FAQ

CUSTOMER SERVICE

DFRobot Distributors
Contact us
Site Map

MY ACCOUNT

Affiliates
Specials
Coupon

Downloaded from Arrow.com.