Datasheet for part number GDE9SF225F0

Our Catalog Part Number: GDE9SF225F0
Our Global Manufacturing Part Number: 111634-0048
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: GD

Product Datasheet	
General	Connector providing high-reliability and moisture protection
Wire Gauge Range AWG	AWG 20
Mating Cycles	500
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	10 mili Ohm max
Operating Temperature	-65°/+150°
Salt Spray Test	48 hours {96 Hrs for Stainless Steel}
Shell Material	Passivated stainless steel
Shell Finish	Stainless steel shell
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	white
Contact Arrangement	9
Gender	Socket, crimp termination
Contacts	delivery without contacts, please order separately
Contact Type	turned
Contact Material	copper alloy
Contact Finish	50 microinch gold over 100 microinch copper
Contact Termination	Crimp
Mounting Method	.120" (3,05mm) Through Hole

Specifications and dimensions subject to change.

Downloaded from Arrow.com.