Part Number : 2037028500
Product Description : FineAdjust Applicator for Mini-Fit TPA 2.0 Crimp Terminals, Double 22 AWG Wires
Series Number : 207127
Status : Active
Product Category : Applicators and Crimp Modules



Documents and Resources

Tooling Specifications

2037028500-000.pdf

TM-638000029-001.pdf

TM-638004900-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for Mini-Fit TPA 2.0 Crimp Terminals, Double 22 AWG Wires
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust,Mini-Fit TPA
Tool Type	Applicator
UPC	195842137233
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Downloaded from Arrow.com.

Physical

Net Weight	1.000/g

Applicable Parts

Description	Part Number
Mini-Fit TPA2/Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), Double 22+22 or Single 20-18 AWG, 2.10-2.85mm Insulation Diameter, Reel	1727184111
Mini-Fit TPA2/Sigma Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), Double 22+22 or Single 20-18 AWG, 2.10-2.85mm Insulation Diameter, Reel	1727184121
Mini-Fit TPA2/Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), Double 22+22 or Single 20-18 AWG, 2.10-2.85mm Insulation Diameter, Reel	2029884141
Mini-Fit TPA2/Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), Double 22+22 or Single 20-18 AWG, 2.10-2.85mm Insulation Diameter, Reel	2029884241
Mini-Fit TPA2/Sigma Male Crimp Terminal, Brass, Pre-Plated Tin (Sn), Double 22+22 or Single 20-18 AWG, 2.10-2.85mm Insulation Diameter, Reel	1727654121
Mini-Fit TPA2/Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), Double 22+22 AWG or Single 20-18 AWG, 2.10-2.85mm Insulation Diameter, Reel	2030704141
Mini-Fit TPA2/Sigma Male Crimp Terminal, Copper Alloy, Post-	2030704241

Downloaded from Arrow.com.

Plated Tin (Sn), Double 22+22 AWG or Single 20-18 AWG, 2.10-2.85mm Insulation Diameter, Reel	

Downloaded from Arrow.com.