




**Part Number :** [191930097](#)  
**Product Description :** VersaKrimp Ring Tongue  
Terminal for 12-10 AWG Wire, Closed-Brazed Barrel,  
Stud Size 3/8" (M9), Carton  
**Series Number :** 19193  
**Status :** Active  
**Product Category :** Ring and Spade Terminals  
**Engineering Number :** C-301-38

Documents & Resources

**Drawings**  
[191930097 sd.pdf](#)  
**Specifications**  
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800755049312

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	3.116/g
Packaging Type	Carton
Stud Size	3/8" (M9)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	5.76mm max.
Wire Size (AWG)	10, 12
Wire Size mm <sup>2</sup>	4.00-6.00

---

# Application Tooling

## Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm <sup>2</sup> - 0.5mm <sup>2</sup>	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>

---

This document was generated on Sep 17, 2025