



Part Number : [638194600](#)
Product Description : PremiumGrade Hand Crimp
Tool for CLIK-Mate Wire-to Board Terminals, 28-24
AWG and 0.08 and 0.20mm² Wire
Series Number : 207129
Status : Obsolete
Product Category : Crimp Presses and Crimp Hand
Tools



Documents & Resources

Tooling Specifications

- [ATS-6381946HM-001.pdf](#)
- [TM-638000029-001.pdf](#)
- [TM-638000029DE-001.pdf](#)
- [TM-638000029SP-001.pdf](#)
- [TM-638000029FR-001.pdf](#)
- [TM-638000029IT-001.pdf](#)
- [TM-638000029JP-001.pdf](#)
- [TM-638000029KR-001.pdf](#)
- [TM-638000029MY-001.pdf](#)
- [TM-638000029PL-001.pdf](#)
- [TM-638000029RU-001.pdf](#)
- [TM-638000029SK-001.pdf](#)
- [TM-638000029TH-001.pdf](#)
- [TM-638000029VN-001.pdf](#)
- [TM-638000029CN-001.pdf](#)
- [TM-638000029TW-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant

EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per ED/61/2018 (27 June 2018)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for CLIK-Mate Wire-to Board Terminals, 28-24 AWG and 0.08 and 0.20mm ² Wire
Comments	See Tooling Specification (PDF) Above; Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	PremiumGrade

Tool Type	Hand Crimp Tool
UPC	883906422905
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

Physical

Net Weight	428.885/zg
------------	------------

Applicable Parts

Description	Part Number
CLIK-Mate 1.50mm Pitch Crimp Terminal, Male, 0.10µm Gold Plating, 26-24 AWG, Reel	<u>2130281000</u>
CLIK-Mate 1.50mm Pitch Crimp Terminal, Male, 0.10µm Gold Plating, 26-24 AWG, Bag	<u>2130281100</u>
CLIK-Mate 1.50mm Pitch Crimp Terminal, Male, 0.38µm Gold Plating, 26-24 AWG, Reel	<u>2130283000</u>
CLIK-Mate 1.50mm Pitch Crimp Terminal, Male, 0.38µm Gold Plating, 26-24 AWG, Bag	<u>2130283100</u>
CLIK-Mate 1.50mm Pitch Crimp	<u>2130287000</u>

Terminal, Male, 0.76µm Gold Plating, 26-24 AWG, Reel	
CLIK-Mate 1.50mm Pitch Crimp Terminal, Male, 0.76µm Gold Plating, 26-24 AWG, Bag	<u>2130287100</u>
CLIK-Mate 1.50mm Pitch Crimp Terminal, Male, Tin Plating, 28-24 AWG, Reel	<u>5025790000</u>
CLIK-Mate 1.50mm Pitch Crimp Terminal, Male, Tin Plating, 28-24 AWG, Bag	<u>5025790100</u>

This document was generated on Sep 21, 2025

Obsolete