
MTC100-SH1-R32 Product Details



MTC100-SH1-R32

TE Internal Number: 192489-000

Active

View 3D PDF

MTC Crimp Connector Shells, Inserts and Contacts

Not EU RoHS or ELV Compliant

Product Highlights:

- Connector
- Connector Style = Receptacle
- Jackscrew Mating Hardware
- Not Boxmount
- Without Flange

View all Features

Quick Links
- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Documentation & Additional Information

Product Drawings:
- Shell, Plug and Receptacle MTC100 Series (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files: (CAD Format & Compression Information)
- 2D Drawing (DXF, Version U)
- 3D Model (IGES, Version U)
- 3D Model (STEP, Version U)

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Type = Connector
- Shell Size = 25.4 [1.0]

Mechanical Attachment:
- Flange = Without
- Panel Gasket = Without

Electrical Characteristics:
- Boxmount = No

Contact Features:
- Option = With Cable Clamp and With Ears On Shell
- Plating Material = Cadmium

Housing Features:
- Connector Style = Receptacle
- Housing Type = EME Mount

Industry Standards:
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

Conditions for Usage:
- Applies To = Cable

Other:
- Mating Hardware = Jackscrew
- Brand = Raychem

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved | Privacy Policy

Provide Website Feedback

Downloaded from Arrow.com.