
Part Number : 2037022700
Product Description : FineAdjust Applicator for Insulation OD 4.40-5.30mm, 12-10 AWG
Series Number : 207127
Status : Active
Product Category : Applicators and Crimp Modules



Documents and Resources

Tooling Specifications

2037022700-000.pdf

TM-638000029-001.pdf

TM-638004900-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for Insulation OD 4.40-5.30mm, 12-10 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust,Mini-Fit Sr.
Tool Type	Applicator
UPC	195842624672
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Downloaded from Arrow.com.

Physical

Net Weight	4672.002/g

Mates With / Use With

Use with Part(s)

Description	Part Number
TM-2000 Universal Press	638008300
TM-2000 Universal Press (Europe 220V)	638008400
TM-3000 Universal Crimp Press, 120AC 50/60Hz, Used for product up to 10 AWG	638017200
TM-3000 Universal Crimp Press, 220AC 50/60Hz, Used for product up to 10 AWG	638017300
TM-4000 Universal Crimp Press, 240AC 50/60Hz, Used for product up to 4 AWG	638017600
Use With	Most Industry Standard Presses or Wire Process Machines

---

Applicable Parts

Description	Part Number
Mini-Fit Sr. Crimp Terminal, Female, 12-10 AWG, Tin (Sn), USE NYE LUBE ON MATING SURFACES	428150011
Mini-Fit Sr. Crimp Terminal, Female, 12-10 AWG, Gold (Au)	428150012
Mini-Fit Sr. Crimp Terminal, Female, 12-10 AWG, Silver (Ag)	428150114
Mini-Fit Sr. Crimp Terminal, Male, 12-10 AWG, Tin (Sn)	428170011
Mini-Fit Sr. Crimp Terminal, Male, 12-10 AWG, Gold (Au)	428170012
Mini-Fit Sr. Crimp Terminal, Male, 12-10 AWG, Tin (Sn)	428170111

Downloaded from Arrow.com.

Mini-Fit Sr. Crimp Terminal, Male, 12-10 AWG, Gold (Au)	428170112
Mini-Fit Sr. Crimp Terminal, Male, 12-10 AWG, Silver (Ag)	428171014
Mini-Fit Sr. Crimp Terminal, Male, 12-10 AWG, Silver (Ag)	428171114

Downloaded from Arrow.com.