Product Details for 863024 -1

No Image Available

863024 -1

Active

LGH Multi -Pin Connectors and Cable Assemblies

RoHS Compliant (Statement of Compliance)

Product Highlights:

- Plug
- Product Style = Kit
- 27 kVDC Operating Voltage
- 7 Position
- Shape = Circular

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- PLUG ASSY, H.V., 7 PIN (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- LGH Circular High Voltage Connector with 2, 3, 4, 6,... (PDF, English)

CAD Files:

- None Available

List all Documents

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Plug
- Product Style = Kit
- Number of Positions = 7
- Shape = Circular
- Prewired = No
- Shielded = No
- Mount Angle = Straight
- Wire Size (mm ² [AWG]) = 0.2 -0.5 ² [24-20]

Mechanical Attachment:

- Flange = Without

Electrical Characteristics:

- Operating Voltage (kVDC) = 27

Body Related Features:

- Mount Type = Free Hanging
- Boot = With
- Boot Type = Straight

Housing Related Features:

- Housing Material = Plastic

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = AMP

© 2006 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.