

★★★★★

0 Reviews

★★★★★

0 Reviews

Need Help?

<

Browse All Products

|

Networking

|

Racks, Cabinets, Panels & Enclosures

|

Racks, Cabinets, and Enclosures



Q-Series Vertical Manager, 7' H X 10" W, Double-Sided

Mount to any standard EIA rack to manage and secure cables

★★★★★

0 Reviews

Product # : QVMD710

Ships in 3-5 business days

1

Add

VISA

MasterCard

AMERICAN EXPRESS

DISCOVER

print

share

chat

- Description
- Features
- Specs
- Support

Product Description

The Q-Series Vertical Manager is simple and fast to assemble, and mounts effortlessly to the Legrand Standard EIA Rack System. Perfect for building networks, it will easily install into a single open rack system or a complete row of open racks. Cables dress cleanly to the front and can also be dressed to the rear using the wire cages, or the optional cable ring kit. The Legrand Vertical Cable Manager is a product designed for versatility, but built for value.

Convenience

Completely tool-less to assemble and installs in minutes. Assembly is tool-less and installation takes just minutes. The lightweight construction and modular manager components make this a one-person job. Cable retention clips allow network installers to separate copper and fiber within the same vertical manager.

Durability

Made from ABS plastics, it has rugged wire cages which double as cable tie locations and has flexible fingers for individual RU cable management.

Product Features

- Double-sided
- Snap fit tool-less assembly
- Lightweight plastic assembly
- Rugged, flexible fingers for individual RU cable management
- Cable management rear wire cage frame
- Mounts to standard EIA 2 and 4-post racks

⚠️

WARNING: Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Specifications

Color :	Black
UPC :	662875963790
Warranty :	5 years
Vendor :	Legrand

Weight :

0.999 LB

Physical Specifications

- Depth: 17.50" (444.50mm)
- Height: 7' (2133.60mm)
- Length: 7' (2133.60mm)
- Width: 10" (254mm)
- Rack Units: 45
- Material 1: ABS Plastic
- RoHS Compliant

Product Support

Downloads

- Download the [Sell Sheet](#)

Info

- About Us
- Order History
- Where To Buy
- More ▾

Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

Have A Question?

- Get help with [Chat](#)
- Call C2G **800.506.9607**
- [f](#) [t](#) [▶](#) [b](#)

