# Power Cords *1584C Series*



## Gallery






RoHS

| 6.5 ft Cord Part No. | 15.5 ft Cord Part No. | Description | Amps | Cord Type | Cord Gauge | Plug Blade Type |
|---|---|---|---|---|---|---|
| **1584C6** | **1584C15** | Straight Blade Molded Plug | 15 | SJT | 14/3 | NEMA 5-15P |
| **1584C6RP** | **1584C15RP** | Straight Blade - 90 Degree - Right Angle Molded Plug | 15 | SJT | 14/3 | NEMA 5-15P |
| **1584C6S20** | **1584C15S20** | Straight Blade Molded Plug | 20 | SJT | 12/3 | NEMA 5-20P |
| **1584C6TW** | **1584C15TW** | Locking Type Molded Plug | 15 | SJT | 14/3 | NEMA L5-15P |
| **1584C6TW20** | **1584C15TW20** | Locking Type Molded Plug | 20 | SJT | 12/3 | NEMA L5-20P |

All cords are SJT or equivalent.

## Input Accessory Cords

| Part No. | Description | Amps | Volts AC | Cord Length | Cord Type | Cord Gauge | Plug Region | Plug Blade Type | Connector Type |
|---|---|---|---|---|---|---|---|---|---|
| **1581C6EU** | European Schuko plug | 10 | 250 | 72.00 | SVT | 18/3 | European | Schuko | IEC 320-C13 |
| **1581C6NA250** | North American Nema 6-15P plug | 10 | 250 | 72.00 | SJT | 18/3 | North America | NEMA 6-15P | IEC 320-C13 |
| **1581C6NA** | North American Nema 5-15P plug | 10 | 125 | 72.00 | SVT | 18/3 | North America | NEMA 5-15P | IEC 320-C13 |
| **1581C6UK** | UK (BS1363) plug | 10 | 250 | 72.00 | SVT | 18/3 | UK | BS1363 | IEC 320-C13 |
| **1581C6IEC** | Male & Female IEC 320-C13 Jumper Cord | 10 | 125 | 72.00 | SVT | 18/3 | Universal | IEC 320-C13 | IEC 320-C14 |

*Data subject to change without notice.*

Downloaded from Arrow.com.

© 2026. Hammond Manufacturing Ltd. All rights reserved.

Downloaded from Arrow.com.