
Product Line

Single Pair Ethernet
ZConnect
Ceres
X-Lok
M Series
Accessory
M5
Guided M8
M8
M10.5
M12 (A)
M12 (B)
M12 (D)
M12 (I)
M12 (K)
M12 (L)
M12 (S)
M12 (T)
M23
FLOS & FLOS+
Power
RBL
HS-Lok
NMEA 2000
Heavy Duty Shielded
RJ
USB
SSL
HDMI
DVI
Fiber Optic
RF
Cable Joiner
Cable Gland
Pressure Relief Vent
LED Light Guide
D-Sub





MSDS-04BMMC-SR7001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Metal, Shielded

Jacket Material: N/A

Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity − 1 + Check Stock

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type | Search



M Series, Accessory,...
CAP-WBCMSMA2
-40°C ~ +105°C



M Series, Accessory,...
CAP-WBDMSMA2
-40°C ~ +105°C



M Series, Accessory,...
CAP-WBHMSMA1
-40°C ~ +105°C



M Series, M12, D Code,...
M12D04FL-12DMR-...
-20°C ~ +105°C

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current: **4A**	Connector Type: **Field Installable**
Shielded: **Metal, Shielded**	No. of Contacts: **04**
Connector Gender: **Male**	Backshell: **Right Angle**
Mating Style: **Screw Thread**	IP Rating: **IPX7**
Assembly Style: **Crimp**	

More Options

People Also Bought

Downloaded from Arrow.com.