



- NOTES : (UNLESS OTHERWISE SPECIFIED)**
- MATERIAL :**
 - NUT : ZINC ALLOY, NICKEL PLATED.**
 - CLAMP INSERT : THERMOPLASTIC UL94 V-0.**
 - EMI SHIELDING RING : STAINLESS STEEL.**
 - BACK SHELL : ZINC ALLOY, NICKEL PLATED.**
 - O-RING: SILICONE RUBBER.**
 - GROMMET : RUBBER.**
 - ROHS COMPLIANT.**
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.**

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASED DRAWING	JAN-18-2014	ARROW	TOMMY

P/N	SHIELDING RING	CABLE RANGE
RT0L-18CG-C1	WITHOUT	Ø9.0-Ø14.5mm
RT0L-18CG-C2	WITHOUT	Ø13.5-Ø17mm
RT0L-18CG-S1	WITH	Ø9.0-Ø14.5mm
RT0L-18CG-S2	WITH	Ø13.5-Ø17mm

QUANTITY		PART NUMBER		DESCRIPTION		ITEM
MATERIALS LIST						
UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE		Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036
1) All dimensions are in metric(mm).		DRAWN: ARROW		JAN-17-2014		
2) Tolerances are as follows:		CHECKED:				
1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08		ENGINEER:				
3) Note reference =		APPROVAL:				
MATERIAL SPECIFICATIONS:		CUSTOMER:				
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		SIZE		REVISION
NEXT ASSY:				B C-		B1
				SCALE: NONE		
				SHEET 1 OF 1		

TITLE: ECO-MATE,CORD GRIP SIZE 18
DWG NO: RT0L-18CG-xx
REV: B1
SH: 1
OF: 1