© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

RUGGEDIZED BACKSHELLS & ADAPTERS



✔ Active

TE CONNECTIVITY (TE)

TXR40BB90-2016AI

Raychem | TCR , Terminator

TXR40BB90-2016AI
TE Internal Number: D97762-000
Alias ID: 6-1202086-0

Not EU RoHS Compliant
Not EU ELV Compliant

Cable Diameter Range 12.7 – 20.3 mm [.5 – .8 in]

Material Nickel Aluminum Bronze

Adapter Plating Material Cadmium (AMS-QQ-P-416 Type II, Class 3)

Adapter Angle 90

Style Tinel-Lock Adapter

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

TINEL LOCK BACKSHELL
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Downloaded from Arrow.com.

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

5-1654025-5_sec6_Adapters

PDF

English

Product Specifications

Product Specification

Braid Termination Using A Tinel Lock Ring Installed Using A Resistance Heater.

PDF

English

PERFORMANCE SPECIFICATION Tinel-Lock Rings, Heat Recoverable For Braid Termination

PDF

English

ASSEMBLY GUIDE For Tinel -Lock Rings, Heat Recoverable For Braid Temination

PDF

English

General Information Package For Tinel-Lock Adapters

PDF

English

General Harness Repair Manual

PDF

English

Adapter Finish Specifications

PDF

English

Product Environmental Compliance

REACH Substance Communication Document

RSCD_Cadmium

PDF

English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Downloaded from Arrow.com.

Adapter Angle 90
Style Tinel-Lock Adapter
Termination Device Type Side-Entry Tinel-Lock Ring, Tinel-Lock Ring
Connector Shell Size 21, G
Termination Device Included TR16AI
Accessory Type Tinel-Lock Adapter

Body Features

Color Olive Drab
Material Nickel Aluminum Bronze
Adapter Plating Material Cadmium (AMS-QQ-P-416 Type II, Class 3)
TE Adapter Code 40
Adapter Entry Size 16

Termination Features

Overbraid Termination Tinel-Lock Ring

Dimensions

Cable Diameter Range 12.7 – 20.3 mm [.5 – .8 in]
Cable Entry Diameter .2 – 25.4 mm [.01 – 1 in]

Usage Conditions

Operating Temperature Range -65 – 175 °C [-85 – 347 °F]
Salt Spray Resistance (Hr) 500

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.